



## **GH1 ceiling hoist system**

The GH1 ceiling hoist system makes full use of innovative and robust GH3 technology and its design, functionality and cost-effectiveness. The GH1 ceiling hoist system is intended to meet the full range of day-to-day lifting needs. This makes it ideal for use in private homes, sheltered housing or in care homes. The discreet, classic design of the GH1 system means it takes up very little space.

Just as in the GH3 ceiling hoist system for professional use, the GH1 system enables carers to lift and move users without risking back strain.





### **GH1 rail system**

The GH1 ceiling hoist system is available with 3 different types of rails, each specially designed for particular spans and lifting weights. Combining these appropriately makes installation an easy, rapid process.

In addition to rails for mounting on walls and ceilings, the GH1 system features a free-standing rail system. These rails are easy to adjust in both height and width, providing an ideal way to deal with any temporary need for lifting help. The entire rail system can be set up by 1 or 2 people, with no tools needed. The entire system can be made ready for use – and taken down again – in only 10 minutes.

The GH1 ceiling hoist system differs from its GH3 counterpart in that the lifting module does not recharge while mounted on the rail. Instead, recharging is done by placing the control unit (which is linked to the lifting module by cable) in the GH1 recharging dock, which is connected to a mains power supply. Recharging normally only takes 2–3 hours, and a fully charged GH1 lifting module can cope with normal day-to-day lifting for up to two weeks (based on 55 lifts of 85 kg each).

### **GH1 lifting modules**

A GH1 lifting module quickly, safely and effectively lifts weights of up to 205 kg. Quicker lifting frees up more time for all-important nursing and caring duties.

The control system for raising and lowering is easy and intuitive, using a prize-winning, ergonomically correct control unit.

The GH1 lifting module is fitted with the same lifting hanger used in the GH3 ceiling hoist system. This makes it easy and safe to attach the lifting sling, and to use the full range of Guldmann lifting slings and other lifting accessories.

The GH1 lifting module fits into all Guldmann rail systems. Both the lifting module and the rail systems are easy to decorate so that they match or blend into the interior design of the space in which they are used.

The GH1 lifting module complies with all relevant standards, and is extremely safe and reliable in use.

The module is available in different versions with a maximum safe working load (SWL) of 175–205 kg.



**Time to care**

**V. Guldmann A/S**  
Graham Bells Vej 21-23A  
DK-8200 Århus N  
Tel. +45 8741 3100  
Fax +45 8741 3131  
info@guldmann.com  
www.guldmann.com